

# **VIVID**<sup>™</sup>

### UV-A LED Replacement Bulbs

**BLE-LED-100**, **BLE-LED-150** + **BLE-LED-150/F** 

Convert your mercury vapor HID lamp to modern LED technology.



#### LONGEVITY

Rated life is **10x longer** than a mercury vapor HID bulb (with typical use)







#### INSTANT-ON OPERATION No wait time to ge

No wait time to get to full intensity



LOWER LABOR COSTS Eliminates down-time



#### SAFER

Over 50% cooler! 225°F vs. 109°F (HID) (LED)



### **ENVIRONMENTAL**

Less environmental waste with fewer bulbs and energy efficient

The average lifespan of a mercury-vapor bulb when used in NDT inspection is 5,000 hours.

*Upgrade* to the VIVID<sup>™</sup> and reap the benefits of LEDs that last **50,000 hours** (based on average use).

Can be used in custom lamp fixtures that include enclosures.



## COMES WITH PATENTED BULB-SAVER™

Keeps bulb upright in housing and maintains alignment through usage, increasing longevity.








#### **NOMINAL STEADY-STATE UV-A COVERAGE AREA VISIBLE LIGHT MODEL UV-A INTENSITY** at 15 in (38 cm) at minimum **MEASUREMENT** 1,000 µW/cm<sup>2</sup> at 15 in (38 cm) BLE-LED-100 4,700 µW/cm<sup>2</sup> < 1.0 foot-candle 6.5 in (16.5 cm) BLE-LED-150 (with UV-A pass filter) Diameter (11 lux) BLE-LED-150/F

 $\checkmark$ 

Meets standard wavelength and output specifications

C € EK



Works **seamlessly** in conjunction with the following Spectro-UV® HID lamps, saving you both time and money on bulb changes:

LAMP	CURRENT BULB TYPE	REPLACEMENT VIVID BULB
SB-100P Series	100S/M HID Bulb	BLE-LED-100
FC-100 Series	100S/M HID Bulb	DLE-LED-100
BIB-150P Series	BLE-150CS-115/M	BLE-LED-150
	BLE-150BS-115/M	
	BLE-150CS-100/M	
BIB-150P/F Series	BLE-150CS-230/M	BLE-LED-150/F
FC-150/F Series	BLE-150FC-230/M	DLL-LLD-130/I



www.Spectro-UV.com 4 Dubon Ct., Farmingdale, NY 11735 866-230-7305



5605 Freitag Drive Menomonie, WI 54751 PH: 715-235-7222 news@rcon-ndt.com